


2 Hob Portable Unit

CK226



| Specification | | | | | | | | | |
|-------------------------|---------|--|-----|-----|-------------------|---------|----------------------|-------------------|--------------------------|
| Electricity | CK226 | 220V, 60Hz, 1PH | | | Power Consumption | CK226 | 5200 W | | |
| | CK226-A | 208~240V, 50/60Hz, 1PH | | | | CK226-A | | | |
| | CK226-E | 220~240V, 50/60Hz, 1PH | | | | CK226-E | 4800 W | | |
| | CK226-J | 200V, 50/60Hz, 1PH | | | | CK226-J | | | |
| Power Connection | | 2 separate plugs | | | Max Current | | 24 A (L:12A / R:12A) | | |
| Conversion to Calory | | 4492.8 Kcal/h | | | | | | | |
| Warming | | H1 ~ H7 (7 steps) | | | Heating | | | 1 ~ 10 (10 steps) | |
| 7 Warming Steps (H1-H7) | | H1 | H2 | H3 | H4 | H5 | H6 | H7 | (1L Water, using chafer) |
| | | 35℃ | 40℃ | 50℃ | 60℃ | 70℃ | 80℃ | 90℃ | |
| Dimension / Weight | | Product: 700 X 450 X 115 (mm) / 13kg Package: 770 X 520 X 210 (mm) / 15.5kg | | | | | | | |
| Controller Type | | Capactive button (integrated into the unit) | | | | | | | |
| Cookware Diameter | | min : Ø130mm max : Ø300mm | | | Loadable Weight | | 30 Kg | | |
| Recommendation | | Pasta, Egg station, Open kitchen | | | | | | | |
| Functions & Features | | ■ Safety - No vessel : "00" - Over current indication : "E1" - Over voltage indication : "E2" (Above 265V) - Low voltage : "E3" (Below 180V) - Over heated product indication : "E4" (IGBT heat sink temperature above 85°C) - Top glass overheated (empty vessel) : "E6" (Top surface temperature above 260°C) - Unstable power indication: "E7" - Defective PCB indication : "E8" - Defective Working Coil indication : "E9" | | | | | | | |
| Warranty | | 1 year (to be charged in case of user's negligence) | | | | | | | |

Seoul Office: #75, Ahasan-ro 78-gil, Gwangjin-gu, Seoul, Republic of Korea 04969 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412


R&D Center: #209, Goraesan-ro, Wabu-eup, Namyangju-si, Gyeonggi-do, Republic of Korea 12202 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412

DIPO INDUCTION CO., Ltd. / www.dipoele.com

COPYRIGHT©2010 DIPO INDUCTION CO., LTD ALL RIGHTS RESERVED.

2 Hob Portable Unit

CK235



Specification

| | | | | | | | | |
|--|---------|---|-------------------|-----------------|-------------------------|----------------------|-----|--------------------------|
| Electricity | CK235 | 220V, 60Hz, 1PH | Power Consumption | CK235 | 7000 W | | | |
| | CK235-A | 208~240V, 50/60Hz, 1PH | | CK235-A | | | | |
| | CK235-E | 220~240V, 50/60Hz, 1PH | | CK235-E | 6000 W | | | |
| | CK235-J | 200V, 50/60Hz, 1PH | | CK235-J | | | | |
| Power Connection | | 2 separate plugs | Max Current | | 30 A (L:15A / R:15A) | | | |
| Conversion to Calory | | 6048 Kcal/h | | | | | | |
| Warming | | H1 ~ H7 (7 steps) | Heating | | | 1 ~ 10 (10 steps) | | |
| 7 Warming Steps (H1-H7) | H1 | H2 | H3 | H4 | H5 | H6 | H7 | (1L Water, using chafer) |
| | 35℃ | 40℃ | 50℃ | 60℃ | 70℃ | 80℃ | 90℃ | |
| Dimension / Weight | | Product: 700 X 450 X 115 (mm) / 13kg Package: 770 X 520 X 210 (mm) / 15.5kg | | | | | | |
| Controller Type | | Capactive button (integrated into the unit) | | | | | | |
| Cookware Diameter | | min : Ø125mm max : Ø300mm | | Loadable Weight | | 30 Kg | | |
| Recommendation | | Pasta, Egg station, Open kitchen | | | | | | |
| Functions & Features | | Safety | | | | | | |
| | | - No vessel : "00" | | | | | | |
| | | - Over current indication : "E1" | | | | | | |
| | | - Over voltage indication : "E2" (Above 265V) | | | | | | |
| | | - Low voltage : "E3" (Below 180V) | | | | | | |
| | | - Over heated product indication : "E4" (IGBT heat sink temperature above 85°C) | | | | | | |
| | | - Top glass overheated (empty vessel) : "E6" (Top surface temperature above 260°C) | | | | | | |
| - Unstable power indication: "E7" | | | | | | | | |
| - Defective PCB indication : "E8" | | | | | | | | |
| - Defective Working Coil indication : "E9" | | | | | | | | |
| Warranty | | 1 year (to be charged in case of user's negligence) | | | | | | |

Seoul Office: #75, Ahasan-ro 78-gil, Gwangjin-gu, Seoul, Republic of Korea 04969 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412

R&D Center: #209, Goraesan-ro, Wabu-eup, Namyangju-si, Gyeonggi-do, Republic of Korea 12202 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412

DIPO INDUCTION CO., Ltd. / www.dipoele.com

COPYRIGHT©2010 DIPO INDUCTION CO., LTD ALL RIGHTS RESERVED.